

RO-47

1 PORTA
1 DOOR
1 PUERTA
1 PORTE





60
KG



15 a
25 mm

COMPONENTES/ COMPONENTS/ COMPONENTES/ COMPOSANTS

Inclusos no Kit/ Included in the Kit/ Incluidos en el Kit/ Inclus dans le Kit



Conforme aplicação/ As per application
Según la aplicación/ Selon l'application




Recomendados/ Recommended/ Recomendados/ Recommandés




3,5 x 14 CC
Carros inferiores
Bottom carriages
Carros inferiores
Chariots inférieurs

3,5 x 22 CC
Guias e freios
Guides and brakes
Guias y frenos
Guides et freins

Opcionais/ Optional/ Opcionales/ Optionnels




Dispositivo antidescarrilamento
Anti-derailment device
Dispositivo antidescarrilamento
Dispositif anti-déraillement



Amortecedor Comfort 240
Damper Comfort 240
Amortiguador Comfort 240
Amortisseur Comfort 240


CÁLCULO DA PORTA/ DOOR CALCULATION
CÁLCULO DE LA PUERTA/ CALCUL DE LA PORTE



AP= AV-32 mm

Altura da porta (AP)
Door height
Altura de la puerta
Hauteur de la porte

Altura do vão (AV)
Opening height
Altura del vano
Hauteur de l'ouverture




20 a 30 mm


Transpasse indicado
Recommended overlay
Transpase recomendado
Recouvrement recommandé

INSTALAÇÃO/ INSTALLATION/ INSTALACIÓN/ INSTALLATION


1 Furações/ Drillings/ Perforaciones/ Perçages



Alumínio/ Aluminium/ Aluminio/ Aluminium



2 Instale os guias/ Install the guides
Instale las guías/ Installez les guides



Centralize o guia na porta
Center the guide on the door
Centre la guía en la puerta
Centrez le guide sur la porte




Opções de guias
Guide options
Opciones de guías
Options de guides




Amortecedor Comfort 240
Damper Comfort 240
Amortiguador Comfort 240
Amortisseur Comfort 240

Espaçamento do trilho/ Track spacing
Espaciado del riel/ Espacement du rail

RM-030



RM-038




3 Fixe o antidescarrilamento
Secure the anti-derailment device
Fije el dispositivo de antidescarrilamiento
Fixez le dispositif anti-déraillement


Com guia
With guide
Con guía
Avec guide





3,5 x 12 CF
Parafusos recomendados
Recommended screws
Tornillos recomendados
Vis recommandées




- 4 Destaque os posicionadores**
Remove the positioning guides
Retire los posicionadores
Retirez les positionneurs




- 5 Instale os trilhos/ Install the tracks**
Fije los rieles/ Installez les rails




- 6 Fixe o freio no trilho superior**
Attach the brake to the top track
Fije el freno en el riel superior
Fixez le frein sur le rail supérieur




- 7 Encaixe as portas/ Fit the doors**
Encaje las puertas / Insérez les portes



- 8 Regule as portas**
Adjust the doors
Ajuste las puertas
Ajustez les portes



Destrave as molas
Unlock the springs
Desbloquee los muelles
Déverrouillez les ressorts



Regule a altura da porta
Adjust the door height
Ajuste de la altura de la puerta
Réglez la hauteur de la porte

- 9 Regule o antidescarrilamento**
Adjust the anti-derailment device
Ajuste el dispositivo de antidescarrilamiento
Réglez le dispositif anti-déraillement

